




RECOMMENDED P.C.B LAYOUT (TOP VIEW)
TOLERANCES: $\pm 0.10\text{mm}$

说明:

1. 特性:

额定电压 :500V AC MAX

小针额定电流 :5A

大针额定电流 :10A, 20A, 30A, 40A

接触阻抗 :30m Ω MAX.

绝缘阻抗 :3000M Ω MIN. at 500V DC

耐电压值 :1000V AC RMS for 1Minute

温度范围 : -55 $^{\circ}\text{C}$ ~+105 $^{\circ}\text{C}$

盐雾时间 : 48H

2. 材料:

胶芯 : PBT, rated UL94V-0

接触点: 铜合金, 镀金1u"-30u"

铁壳 : SPCC, 前壳镀镍后壳镀锡

铜柱 : 铜合金, 镀镍

螺丝 : 铁合金, 镀镍

额定电流	ØA	PCB孔ØB
10A	Ø1.80	Ø2.00
20A	Ø2.80	Ø3.00
30A	Ø3.30	Ø3.50
40A	Ø3.80	Ø4.00

TOLERANCE TABLE	
.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: DWS-36W4M 公头 直插 全金 铆鱼叉锁螺丝			
DRAWN: LYF	DATE: 2024-01-13	PART. NO.		D-DWS036PM-F000	
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DWS-00037	REV.	A QT00