


SPECIFICATIONS

Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard:PBT
 Max.Processing Temp:180°C for 30-60 seconds
 (200°C for 10 seconds)



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-200D-065-B	版本 REV.	A
			.X±0.30	X.°±3'	审核 CHECK	EVA	品名 TITLE	2.00 Mini Jumper 1*2Pin Close Type	页次 SHEET	1/1
			.XX±0.20		核准 APPROVAL	JADE	客户料号 CUTM.NO.			
			.XXX±0.10		单位 UNITS	MM	比例 SCALE	1:1		