Data sheet

1800.7 KKB 2,5/2



Ceramic terminal

RAL: 9010

Business data

Article number	1800.7
Article name	KKB 2,5/2
GTIN (EAN)	4044211119126
Packaging unit	100
Quantity unit	PC
Unit of weight	G
Customs number	85369010
Country of origin	EU

Data sheet

1800.7 KKB 2,5/2


Technical data


Dimensions	
Length	20 mm
Width	17 mm
Height	17 mm
Ratings	
Rated voltage	450 V
Rated current	32 A
Rated cross-section	4 mm²
Connection data	
Connection principle	Screw connection
Connection position	Lateral
No. of poles	2
Wire cross-section single-core (rigid) / stranded, min.	1.5 mm²
Wire cross-section single core (rigid)/stranded, max.	4 mm²
Wire cross-section stranded, min.	1.5 mm²
Wire cross-section stranded, max.	4 mm²
Wire cross-section stranded with wire-end ferrules, max.	2.5 mm²
Screw head	Slotted
Screw threading	M 3
Further technical data	
Working temperature, min.	-40 °C
Mounting type	Mounting face

Data sheet

1800.7 KKB 2,5/2

Media







Data sheet
1800.7 KKB 2,5/2

Accessories

Screwdriver