


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.11.11	阿树



■SPECIFICATIONS

- Voltage rating:500V AC/DC
- Current rating:1A AC/DC
- Withstanding Voltage:1000V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance: ≤20mΩ
- After environment testing: ≤30mΩ

PART NO.:


X9127 H I-24-PT RE

① ② ③ ④ ⑤ ⑥

- ①Series No
- ②Category:H-HSG
- ③Welding Board Angle:I-HSG+hardware
- ④Row No-Pin No:XX-04P~26P
- ⑤Material:PT-PBT UL94V-0
- ⑥Color: RD-purplish red
RE-Red Color

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
4	8.45	2.54	16	23.69	17.78
6	10.99	5.08	18	26.23	20.32
8	13.53	7.62	20	28.77	22.86
10	16.07	10.16	22	31.31	25.40
12	18.61	12.70	24	33.85	27.94
14	21.15	15.24	26	36.39	30.48

X9127HI-24-PTRE	Red	PBT UL 94V-0	Brass	Tin-Plated
X9127HI-24-PTRD	Purplish			
PART NO	Color	Material	Material(Pin)	Finish(Pin)



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	1.27mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.:	X9127HI-24-PTRE
APPROVED		SIZE:	A4	DWG NO.:	X-X9127HI-24-PTRE