





RoHS

SPECIFICATIONS

Rated Current:3.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°C to +105°C

Contact Material:Brass  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001	9.0		7.1	8.5	5.0
002					

深圳市连盛精密连接器有限公司

				OPERATION		DRAW		SCALE		FIT	
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM	TOL	APPROVE	SHEET	PROJ.	UNIT	mm
A0	2012.03.28	NEW DRAWING			X.XXX	±0.10	CHECK	1/1			
					X.X	±0.30					
					X.XX	±0.20					
					Angle	±3°					

PART NO.		1020300870
TITLE:		2.54FH H=8.5 W=5.0 2*21P SMT=7.1 总高9.0 U-A型 AU1U 青铜 PA6T