



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)



SPECIFICATIONS

Current Rating:0.75 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40°to+105°
Insulator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
BX-PM1.0-1-01PU-W	1	0.00	1.00
BX-PM1.0-1-02PU-W	2	1.00	2.00
BX-PM1.0-1-03PU-W	3	2.00	3.00
BX-PM1.0-1-04PU-W	4	3.00	4.00
BX-PM1.0-1-05PU-W	5	4.00	5.00
BX-PM1.0-1-06PU-W	6	5.00	6.00
BX-PM1.0-1-07PU-W	7	6.00	7.00
BX-PM1.0-1-08PU-W	8	7.00	8.00
BX-PM1.0-1-09PU-W	9	8.00	9.00
.....
BX-PM1.0-1-40PU-W	40	(PIN-1)	(PIN)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-PM1.0-1-NPU-W		版本 REV.	A
			X.±0.30	X.*±5°	审核 CHECK	EVA		品名 TITLE	1.0FH H2.0 1xNPin SMT W1.5 UM PC2.8 PB2.3 6T (标准)		页次 SHEET	1/1
			.X±0.20	.X*±1°	核准 APPROVAL	JADE		客户料号 CUTM.NO.				
			.XX±0.10	.XX*±0.5°	单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)			