Data Sheet

Coaxial Panel Connector
13_BMA-50-0-2/199_N

Description

Straight panel receptacle plug, flange mount



Interface standards
IEC 60169-33_MIL-STD-348A/321

Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Number of matings	1000
Weight	0.0025 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	

Related Documents

Catalogue drawing	DCA-00011086

Ordering Information

Single package	13_BMA-50-0-2/199_NE

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.

Document: DOC-0000188706 P / PDO C / date of publication: 28.03.2020 04:33:58 / uncontrolled copy