









P. C. B Layout
(Copper-sided view)



Nut



Washer



Plug

SPECIFICATION

1. Rating : DC 30V 3A.
2. Contact resistance: $\leq 50m\Omega$.
3. Insulation resistance: $\geq 100M\Omega$ (DC500V).
4. Withstanding voltage: 500VAC .
5. Insertion and extraction force: 3-30N.
6. life test: 5,000 cycles.
7. Operation temperature range: $-25^{\circ}C \sim 85^{\circ}C$.
8. Sign"* "is importance dimension.

PIN	$\phi 2.5$		
-----	------------	--	--

Model NO.	DC-025BM-01
Schematic	
CIRCUIT DIAGRAM	

9	WASHER	STEEL	1	Ni-PLATED					
8	NUT	BRASS	1	Ni-PLATED					
7	WASHER	BAKELITE	2	RED					
6	PIN	BRONZE	1	Ni-PLATED					
5	BUSHING	BRASS	1	Ni-PLATED					
4	SHUNT TERMINAL ④	BRASS	1	Sn-PLATED					
3	TIP SPRING ②	PBS	1	Sn-PLATED					
2	CENTER PIN TERMINAL ①	BRASS	1	Sn-PLATED					
1	HOUSING	PBT	1						
NO.	PART	NAME	MATERIAL	QTY	FINISHING				



DONGGUANG HAOYU ELECTRONICS CO., LTD
东莞市弘皓电子有限公司

PRO.AGL: REV :A0