
Data sheet

27110.3 PAP 6/3A OG



End plate, Width: 1.5 mm, Colour: Orange

Business data

Article number	27110.3
Article name	PAP 6/3A OG
GTIN (EAN)	4044211224776
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	3.1 g
Weight per piece (including packaging)	3.3 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	27110.6
Product description	End plate

Data sheet

27110.3 PAP 6/3A OG

Technical data

Dimensions	
Length	74.1 mm
Width	1.5 mm
Height	36 mm
Materials	
Material	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	120 °C
Environmental Product Compliance	
REACH Candidate Substance Note	No

Data sheet

27110.3 PAP 6/3A OG

Media




Accessories

Terminal blocks



Protective earth terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
27021.2	PSL 6/3A GNYE	4044211223960	50 ST



Feed-through terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Grey


Article number	Article name	GTIN (EAN)	Packaging unit
27020.6	PRK 6/3A GR	4044211223953	50

##INVERSE##CONTA-CONNECT



Protective earth terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
27021.2	PSL 6/3A GNYE	4044211223960	50 ST



Feed-through terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
27020.6	PRK 6/3A GR	4044211223953	50