



End plate, Width: 1.5 mm, Colour: Green

Business data

Article number	<u>27110.1</u>
Article name	PAP 6/3A GN
GTIN (EAN)	4044211224752
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	3.1 g
Weight per piece (including packaging)	3.3 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	27110.6
Product description	End plate

Technical data

Dimensions

Length	74.1 mm
Width	1.5 mm
Height	36 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	120 °C

Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media



Accessories

Terminal blocks



Protective earth terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27021.2</u>	PSL 6/3A GNYE	4044211223960	50 ST



Feed-through terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27020.6</u>	PRK 6/3A GR	4044211223953	50

##INVERSE##CONTA-CONNECT



Protective earth terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27021.2</u>	PSL 6/3A GNYE	4044211223960	50 ST



Feed-through terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 6 mm², Width: 8.1 mm, Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27020.6</u>	PRK 6/3A GR	4044211223953	50