

CT2131

Banana Plug Test Lead, Silicone

4 mm Stacking Banana Plug to Stacking Banana Plug Test...

Description

4 mm Stacking Banana Plug to Stacking Banana Plug Test Lead. Highly flexible Silicone lead w. Lead for all applications. Stacking feature allows for multiple connections.

- Materials: Body: Polyamide (Nylon); Contact: Brass, Nickel Plt.
- Banana Contact: BeCu, Nickel Plt.
- Available in 6 standard lengths



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Datasheet

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	33 V AC / 70 V DC
Voltage, Max	1,200 V AC/DC
Current, Max	12 A
Resistance, Max	55 milliohms
Jacket Material	Silicone
Conductor Area	0.75 mm ²
Wire Gauge	18 AWG
Stranding (# x dia.)	195 x 0.07 mm
Jacket OD	3.7 mm (0.146")
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

