




SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60seconds
(260°C for 5seconds)

P/N	PIN	DIM.A	DIM.B
XY-PZ2.54R-01-01P	1	0.00	2.54
XY-PZ2.54R-01-02P	2	2.54	5.08
XY-PZ2.54R-01-03P	3	5.08	7.62
XY-PZ2.54R-01-04P	4	7.62	10.16
XY-PZ2.54R-01-05P	5	10.16	12.70
XY-PZ2.54R-01-06P	6	12.70	15.24
XY-PZ2.54R-01-07P	7	15.24	17.78
XY-PZ2.54R-01-08P	8	17.78	20.32
XY-PZ2.54R-01-09P	9	20.32	22.86
.....			
XY-PZ2.54R-01-40P	40	(PIN-1)X2.54	(PIN)X2.54



RECOMMEND P.C.B. LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

DIMENSION in mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.3	X.*± 5°	APR. Alex	TITLE: 2.54PH H2.5 1xnPin 90度 PC3.0 PA6.0 PB4.3 L13.8 6T 物料			
.XX±0.2	.X*± 1	CHK. Jack	DWG NO. XY-PZ2.54R-01-NP			
.XXX±0.1	.XX*± 0.5	DRA. Can	PROJ. 		CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A