





SPECIFICATIONS :

MATERIAL:

1.HOUSING MATERIAL: PA9T,UL94V-0,COLOUR:BLACK
UL No.E90350(The Supplier-KURARAY PA9T GN2330#)
2.CONTACT MATERIAL: PHOSPHOR BRONZE ϕ0.46mm
3.PLATING: 3u"GOLD PLATING AND NICKLE PLATING OVERALL

ELECTRICAL:


1.VOLTAGE RATING: 125Vac RMS .
2.CURRENT RATING: 1.5AMP .
3.CONTACT RESISTANCE: 30mΩ MAX .
4.INSULATION RESISTANCE: 500MΩ MIN @ 500Vdc .
5.DIELECTRIC WITHSTANDING VOLTAGE: 1000Vac RMS 50Hz 1MIN.


MECHANICAL:

1.DURRABILITY : 750 CYCLES MIN.
2.INSETION FORCE: 2.2Kgf MAX.
3.RETENTION STRENGTH : 7.7Kgf MIN BETWEEN JACK AND PLUG.

ENVIRONMENTAL:

1.STORAGE TEMPRATURE : -40°C TO 85°C.
2.OPERATION TEMPRATURE : -40°C TO 85°C.





PCB LAYOUT

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CANKEMENG INDUSTRIAL CO.,LTD	
CHECKED:	DATE:	TITLE: RJ11-6P/6C 5JA 1*1 全塑 弯插 耐高温	
DRAWN: YKX	DATE: 2026-07-14	PART. NO.	R-RJ11R06P-AT01
		UNIT mm / SCALE free	
		FILE NO. Ckmtw-RJ11-0106	REV. A / KC01