



General Specification
 Current Rating: 1.5A DC /Contact, 20mA DC for LED signals
 Voltage Rating: 125V AC /Contact, 2.0 volts DC for LED signals
 Operating Environment: -20°C~+70°C
 Standard Temperature: -40°C~+85°C
 Humidity: 20~70%
 Contact Resistance: ≤30mΩ
 Insulation Resistance: ≥500MΩ
 Dielectric Strength: 500V AC / (50HZ) /Min
 Mating And Unmating Force: 3~20N
 Durability: 750 Cycles Min

Material Specification
 Housing :Thermo-plastic, UL94V-0.
 Contact :Alloy Copper
 Shield :Alloy Copper
 Please refer to the customer drawing when customer has specified

PCB LAYOUT
 RECOMMENDED

网络插座外形图

绘图:	梁飞	日期:	2022.4.11
审核:	陈伟	日期:	
核准:	朱华	日期:	

序号	名称	材料	数量	镀层/颜色	备注
3	插针	PHOSPHOR BRONZE	16	FU"	
2	右分体	PA46	1	BLACK	
1	左分体	PA46	1	BLACK	

温州瑞川电子有限公司
 WEN ZHOU RUI CHUAN ELECTRONIC CO., LTD.

品名: RCH-56-31-12(全塑无灯)
 料号: 563112-80000010AB30 (RC00168)
 型号: RJ45
 图号:
 单位:mm 比例: 1:1 纸张: A4

版本	1	变更履历	2	3	变更单号	该图面供温州瑞川电子有限公司内部使用,不得私自复印
A/0		新出版发行				