


Single color electrical schematic diagram
单色电气原理图



Installation View
安装视图

| | | | | |
|-----|------|----------|-------------|-------|
| A4 | | | | |
| A3 | | | | |
| A2 | | | | |
| A1 | | | | |
| REV | DATE | REVISION | DESCRIPTION | ISSUE |









| | |
|------------------|--------|
| COMMON TOLERANCE | |
| X.XX | ± 0.10 |
| X.X | ± 0.15 |
| X | ± 0.25 |
| ANGULAR | — |

| | | | | |
|----------|--------|------------|------|-------------------------|
| UNIT | MM | PROJECTED | | PRODUCT NAME: |
| DRAWN BY | FUYUAN | CHECKED BY | COCO | MODEL NO: TP91650P224RS |
| DATE | 2019 | APPROVAL B | ALEN | Https: www.rocpcu.tw |

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission



| | | | | |
|-----|------|----------|-------------|-------|
| A4 | | | | |
| A3 | | | | |
| A2 | | | | |
| A1 | | | | |
| REV | DATE | REVISION | DESCRIPTION | ISSUE |



| | |
|------------------|--------|
| COMMON TOLERANCE | |
| X.XX | ± 0.10 |
| X.X | ± 0.15 |
| X | ± 0.25 |
| ANGULAR | — |

| | | | | |
|----------|--------|------------|------|-------------------------|
| UNIT | MM | PROJECTED | | PRODUCT NAME: |
| DRAWN BY | FUYUAN | CHECKED BY | COCO | MODEL NO: TP91650P224RS |
| DATE | 2019 | APPROVAL B | ALEN | Https: www.rocpcu.tw |

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

材质参数

| | | | | |
|----------|--------------------------|---------------------|-----------|--------------------|
| 10 | luminous zone 发光区 | PC 塑料 | 1 | |
| 9 | LEDpin LED脚 | Brass 黄铜 | 1 | Silvering 镀银 |
| 8 | Base 底座 | PA46 | 1 | |
| 7 | Pin 引脚 | Brass 黄铜 | 1 | gold-plating 镀金 |
| 6 | Contact material 接触材质 | silver alloy 银合金 | 1 | Silvering 镀银 |
| 5 | LED Base LED基座 | PBT | 1 | |
| 4 | Arm nut 固定螺帽 | Brass 黄铜 | 1 | nickeling 镀镍 |
| 3 | Oring O型圈 | Silica gel 硅胶 | 1 | |
| 2 | Housing 外壳 | SUS 不锈钢 | 1 | |
| 1 | Key 按键 | SUS 不锈钢 | 1 | |
| NO 序号 | Part name 部件名 | Material 材料 | QTY 数量 | Remark 备注 |

| | | | | | | | | | | |
|-----|------|----------------------|--|------------------|---------|---|--------|------------|---|-------------------------|
| A4 | | |  <p style="margin: 0;">台普 ROCPU</p> | COMMON TOLERANCE | | UNIT | MM | PROJECTED |  | PRODUCT NAME: |
| A3 | | | | X.XX | ± 0.10 | DRAWN BY | FUYUAN | CHECKED BY | COCO | MODEL NO: TP91650P224RS |
| A2 | | | | X.X | ± 0.15 | DATE | 2019 | APPROVAL B | ALEN | Https: www.rocpu.tw |
| A1 | | | | X | ± 0.25 | ROCPU TECHNOLOGY CO.,LTD | | | | |
| REV | DATE | REVISION DESCRIPTION | | ISSUE | ANGULAR | Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission | | | | |