1437024-5 ✔ ACTIVE

AMP-LATCH

TE Internal #: 1437024-5


TE Internal Description: 622-2031=FSKT IDC S 20 SR

Female Socket Connectors: Strain Relief

View on TE.com >

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Connector Accessories >

Female Socket Connectors: Strain Relief



Flat Flexible Cable Accessory Type: **Strain Relief Cover**

Number of Positions: **20**

All Female Socket Connectors: Strain Relief (14)

Features

Product Type Features

Flat Flexible Cable Accessory Type	Strain Relief Cover

Configuration Features

Number of Positions	20

Body Features

Primary Product Material	Glass-Filled Polyester
Primary Product Color	Blue

Dimensions

Product Length	29.9 mm

Industry Standards

UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	50
Packaging Method	Package

Other

Connector Accessory Comment	Female Socket Connector

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts




TE Part # CAT-AM74-UN384H
AMP-LATCH UNIVERSAL HEADERS



TE Part # 2-1761605-7
IDC LOW PRO HDR 20P RA BLUE




TE Part # 1761607-7
IDC LOW PRO HDR 20P RA LG LAT



TE Part # 2-1761606-7
IDC LOW PRO HDR 20P VERT LG LA




TE Part # 2-1761603-7
IDC LOW PRO HDR 20P VERT BLUE




TE Part # 5103310-5
A/L LOW PRO HDR 20P RA BLACK




TE Part # 5103311-5
A/L LOW PRO HDR 20P RA BLACK




TE Part # 1761606-7
IDC LOW PRO HDR 20P VERT LG LAT BLK




TE Part # 2-1761607-7
IDC LOW PRO HDR 20P RA LG LAT



TE Part # 5103309-5
A/L LOW PRO HDR 20P VERT BLACK




TE Part # 5103308-5
A/L LOW PRO HDR 20P VERT BLACK



TE Part # 1-111446-8
020 UNIV I/O 30DP NO EARS




TE Part # 1-111504-7
020 UNIV I/O 30DP NO EARS LTCH



TE Part # 5104338-4
A/L LOW PRO HDR 20P VERT HT



TE Part # 5111448-4
020 UNIV I/O 30DP SLOT




TE Part # 2-1761679-7
IDC LOW PRO HDR 20P VERT BLUE




TE Part # 5104340-4
A/L LOW PRO HDR 20P RA HT GRAY



TE Part # 1761686-7
IDC LOW PRO HDR 20P VERT LG LAT



TE Part # 2-1761712-7
IDC LOW PRO HDR 20P RA LG LAT



TE Part # 2-1761711-7
IDC LOW PRO HDR 20P VERT LG LA

Customers Also Bought



TE Part #HDP24-18-14PN
REC, 14P, BLK, N, 16, P



TE Part #W2S-P012
WEDGE LOCK, 2P, PLG, GRN, SL RET, DT



TE Part #5205817-1
KIT SCREWLOCK FEMALE



TE Part #770580-1
10P MINI UMNL PLUG HSG



TE Part #170359-3
MINI UNIVERSAL M-N-L PIN



TE Part #42452-2
187 FASTON REC 20-16 AWG TPBR



TE Part #C32547-000
NC-191064-10-9

Documents

Product Drawings

622-2031=FSKT IDC S 20 SR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1437024-5_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1437024-5_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1437024-5_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Ribbon Cable Interconnect Solutions

English