


ROHS


Http://www.krhro.com





Schematic(Shorting)





P.C.B layout

NO.1	
PART NO	H
K3-2320T-G3	3.0
K3-2320T-G4	4.0
K3-2320T-G5	5.0
K3-2320T-G6	6.0
K3-2320T-G7	7.0
K3-2320T-G8	8.0
K3-2320T-G9	9.0

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑦	Steel ball	——	1	PBS	Ni Plated	————
⑥	Spring	——	4	Steel wire	————	————
⑤	Contact	——	2	Brass Strip	Ag Plated	————
④	Terminal	——	8	Brass Strip	Ag Plated	————
③	Base	——	1	NYLON	Black	————
②	Cover	——	1	Steel	Ni Plated	————
①	Knob	——	1	NYLON	Black	————

APPROVALS		DATE	
DRAWN	LIUCAN	2023.10.25	
CHECKED			TITLE: TOGGLE SWITCHS
APPROVALS			PART NO. K3-2320T-G□

TOLERANCES ARE: 30~以上 ±0.30; 10~30 ±0.20; 5~10 ±0.15; ~ 5 ±0.10; ANGLE ±2°

UNIT: mm | SCALE: 1:1 | PROJ: | DRAWING NO. ———— | SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
————	A	————	NEW	————	————	————