




NOTES:

Rating:DC 30V 5A

Contact:Resistance100mΩ Max.

Operating temperature: -20℃~70℃

Operating force: 3-20N

Operating Life: 5,000cycles

PIN	Item number
Ø2.0	DC-044A-N200
Ø2.5	DC-044A-N250

6	PIN	1	HPB50-1	MB: Cu Cu/Sn PLATE
5	TIP SPRING	1	SUS II=0.2	MB: Cu Cu/Sn PLATE
4	SHUNT SPRING1	C2680 T=0.3	MB: Cu Cu/Sn PLATE	
3	RERMDNAI	1	C2680 T=0.3	MB: Cu Cu/Sn PLATE
2		1		BLACK
1	HOUSING	1	PBT UL 94V-0	BLACK
LTR	PART NAME	QTY	MATER1AL	

UNLESS OTHERWISE
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS: ANGLES:
X :±0.25 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10

TITLE	PHONE JACKES			
DWN	xiong	PART NO. DC-044A-NXX		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY