


NOTES:







- 1.Circuit: ON-OFF-ON
- 2.Electrical rating: 6A 250VAC (ULCUL;CQC)
10A 125VAC (ULCUL;CQC)
10(4)A 250VAC (VDE)
- 3.Contact resistance: <50mΩ
- 4.Insulation resistance: >100MΩ
(500VDC between open contacts)
- 5.Dielectric strength: >1500V 1 minute
- 6.Color: cover is black, body is black.

Panel cut - out:

X	Dim.Y	Dim.Z
0.75~1.25mm	19.20+0.1/-0	12.80+0.1/-0
1.25~2.0mm	19.30+0.1/-0	12.80+0.1/-0



Circuit of Switch



5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO		
3	→	8	→	X	±0.30				2019.05.20	MAT'L	***		
2	修改VDE刻字 2021.05.13	7	→	X.X	±0.20					MATERIAL NO.			
1	增加卡耳宽度标注	6	→	X.XX	±0.10							DRAWING NO.	REV.
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	东莞市六钧电子五金有限公司				RT-S01-137-L7NBB	WIF117008	A1	