




修订 REV A0	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
		NEW DWG		2016-03-12


B型:



SPECIFICATIONS

Current Rating: 2Amps
 Insulator resistance: 5000 Megchms min.
 Dielectric Withstanding: AC 500V
 Operating Temperature: -40° ~ +105° C
 Max Processing Temp: 230° for 30~60 seconds
 (260° for 10 seconds)
 Contact Material: Brass
 Insulator Material: NYLON-6T




UNSPECIFIED TOLERANCE: ±0.20



PCB LAYOUT

Plastic Base

Type	
H	1.0
PA	4.0±0.2
PC	5.5±0.2

 深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话: 0755-27111216 传真: 0755-29940187		TITLE: 产品名称: B型1.27*1.0 SMT 排针 PA4.0 PBL.5 PC5.5					
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		 		PART NO: 产品编号: HDGC127-PS1-n			
X.X ±0.30	X.X* ±3°	APPD: 核准:	CHECK: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XX ±0.20	X.XX* ±2°	DRAW: 黄艳兰	2016-03-12	1:1	mm	A001	
X.XXX ±0.10	X.XXX* ±1°	绘图:					