

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u~MIN, 表面镀金0.8u~MIN

Contact: Brass, 0.8u~MIN GOLD PLATING OVER ALL
30u~MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C

Temperature Range: -40° C to +105° C


IR炉温度: 265° C (5-10秒)

IR furnace temperature: 265 °C (5-10 seconds).

Ordering Information

B190-1 50 A0 C S B E 1


NO OF PINS	Contact Plating	INSULATOR MATERIAL	BACKING	PACKING
4-100P	Full Gold	Semi-gold	Grey427	PE Bag
A0=0.8u"	BO=0.8U	A: PET	Grey413	Tape & Reel
A1=1u"	B1=1U	B: PA6T	White	Tube
A2=1.5u"	B2=1.5U	C: PA9T	Blue	Tube+CAP
A3=2u"	B3=2U	D: LCP		Tray
A4=3u"	B4=3U			
A5=5u"	B5=5U			
A6=10u"	B6=10U			
A7=15u"	B7=15U			
A8=20u"	B8=20U			
A9=30u"	B9=30U			
S1=Ordinary Tin Plated				
S2= Matte Tin Plated				
S3= Tin-plated High-temperature				



客编:

注意事项

1. 带*为品质检验尺寸



			OPERATION		SCALE		Fit		东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co., Ltd.		
			X.X	+0.25	UNIT		MM				
			X.XX	+0.20	SIZE	A4	DESIGN	周芳杰2020.05.11	PART NO.	B190-150A0CSBE1	
			X.XXX	+0.10	SHEET	1/1	CHECK		TITLE:	2.54间距 塑高9.0 50P 镀普金 PA9T料 180度 黑色 盘装	
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION			DI M	TOL	PROJ.	APPROVE	Customer No.	306003-00149