SIEMENS

Data sheet US2:CNFS364N

Siemens Low Voltage Circuit Protection OEM Disconnect & Accessories. Type: OEM DISCONNECT SWITCH Std: UL/CSA/CE Rating: 400VAC-690VAC 200A Three phase Non-fused Action: Single Throw. O. Cycles: 8,000 O. Temperature: (-20F-120F) AMBIENT TEMPERATURE

General technical data	
fastening method	Panel Mounted
Model	
product brand name	Siemens
product type designation	OEM Disconnect Switch
General product approval	
certificate of suitability	UL/CSA

last modified: 8/23/2022

Subject to change without notice
© Copyright Siemens

Subject to change without notice
© Copyright Siemens