




SPECIFICATIONS

Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240°C for 30-60 seconds
 (260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
XY-PZ2.54R-02-01P	2*1	0.00	2.54
XY-PZ2.54R-02-02P	2*2	2.54	5.08
XY-PZ2.54R-02-03P	2*3	5.08	7.62
XY-PZ2.54R-02-04P	2*4	7.62	10.16
XY-PZ2.54R-02-05P	2*5	10.16	12.70
XY-PZ2.54R-02-06P	2*6	12.70	15.24
XY-PZ2.54R-02-07P	2*7	15.24	17.78
XY-PZ2.54R-02-08P	2*8	17.78	20.32
XY-PZ2.54R-02-09P	2*9	20.32	22.86
.....
XY-PZ2.54R-02-40P	2*40	(PIN-1)X2.54	(PIN)X2.54



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: 2.54PH H2.5 2xnPin 90# PC3.0 PA6.0 PB6.9 L13.8/18.8 6T 特精		
.X \pm 0.35	X.* \pm 5'	APR.	Alex	DWG NO. XY-PZ2.54R-02-NP
.XX \pm 0.2	.X.* \pm 1	CHK.	Jack	PROJ. CUSTOMER DRAWING
.XXX \pm 0.1	.XX.* \pm 0.5	DRA.	Can	SIZE A4 SCALE 1:1 SHEET 1/1 REV. A