






GT-A1502 H M-1 XX X 01

G-Switch

Series No

Connector
H-Housing

M-Male

Housing Colour
W-White

Pin Q' PY
02~15

Row NO
1-Single Row

G-Switch Specification:

- 1.Current rated: 3.0A AC/DC
- 2.Voltage rating: 250V AC/DC
- 3.Withstanding voltage: 500V AC
- 4.Contact resistance: 20mΩ max.
- 5.Insulation resistance:1000MΩ min
- 6.Durability cycle: 50Cycles
- 7.Removal force: 1.0kgf/Pin min
- 8.Operating temperature range: -25°C ~ +85°C

Ordering Information:

Circuit	Dimensions(mm)		Circuit	Dimensions(mm)	
	A	B		A	B
02	4.10	--	09	14.60	12.00
03	5.60	3.00	10	16.10	13.50
04	7.10	4.50	11	17.60	15.00
05	8.60	6.00	12	19.10	16.50
06	10.10	7.50	13	20.60	18.00
07	11.60	9.00	14	22.10	19.50
08	13.10	10.50	15	23.60	21.00

SCALE: 1:1

UNIT: mm

SIZE: A4



Title: Housing 1.50mm Pitch MX Male

Molde Code: GT-A1502HM-1XXX01

DRAWN

CHECKED

APPROVED

DATE

Hu

Chen

Chen

2022.12.28

品赞科技
b-Switch
www.dg-switch.com

REV: A0

SHEET: 1/1



Unless otherwise
General Tolerance:
X ±0.40
X.x ±0.30
X.xx ±0.20
X° ±5°
X.x° ±3°

1	HOUSING	PA66,94V-0	WHITE
NO.	PART NAME	MATERIAL	REMARK