



产品编号 : [193240004](#)

Product Description : Avikrimp Metric Ring Terminal for Stud Size 8 (M4), Red Insulated Barrel, Bag

系列号 : 19324

状态 : Active

Product Category : Ring and Spade Terminals

工程编号 : AA1-821-M4



文件和资源

图纸


[图纸 193240004_sd.pdf](#)

3D 模型和设计文件

[3D模型 193240004_stp.zip](#)

产物环境合规

合规

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2023)3788-DC (14 Jun 2023) |
| EU RoHS | Compliant per EU 2015/863 |

多部分产品合规性声明

- Eu RoHS
- REACH SVHC
- Low-Halogen

多部分行业合规性文件

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

欧盟 RoHS 合格证书

产品详情

常规

| | |
|------|---|
| 状态 | 活动 |
| 类别 | Ring and Spade Terminals |
| 系列 | 19324 |
| 说明 | Avikrimp Metric Ring Terminal for Stud Size 8 (M4), Red Insulated Barrel, Bag |
| 关键字 | Ring Terminal, Ring Terminals |
| 产品系列 | Metric Ring Terminals |
| 产品名称 | Avikrimp |
| 类型 | Ring |
| UPC | 887191290041 |

机构

| | |
|----|--------|
| UL | E32244 |
|----|--------|

物理

| | |
|---------------------|-----------------|
| 筒型 | Closed - Brazed |
| 阻燃性 | 94V-2 |
| 绝缘 | Nylon (PA) |
| 材料 - 金属 | Copper Alloy |
| 材料 - 接合部位电镀 | Tin |
| 净重 | 0.815/g |
| 包装形式 | Bag |
| 螺柱规格 | M4 |
| 线径规格 (AWG) | 不适用 |
| 线缆尺寸mm ² | 0.50-1.00 |

进程

| | |
|----|-----|
| 无铅 | 不适用 |
|----|-----|

施工工具

全局

| 描述 | 产品编号 |
|--|-------------------|
| PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm ² (Rings, Spades, Hooks, Block Spades and Flanged Spades) | <u>0640010100</u> |
| Crimp Head for the AT-200 Pneumatic Hand Tool | <u>0640050100</u> |
| ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool | <u>0640160036</u> |