


LOC		DIST		REVISIONS				
G	14	P	LTR	DESCRIPTION		DATE	OWN	APVD
			A	ECR-24-230393		21FEB2025	LP	DSC

AMP
WIRE RANGE

16-14HD AWG
SOLID OR STRANDED


 LR7189
Certified

16-14HD AWG
SOLID OR STRANDED



500	LOOSE PEICE	184269-1
QTY	PACKAGING TYPE	PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		RECOMMENDED OPERATING TEMPERATURE: 170° C [338°F]MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm ² [2,050-5,180] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 30MAY96	 TE Connectivity						
		CHK MJ SPICER 31MAY96							
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		TERMINAL, RING TONGUE, SOLISTRAND™, BENT 90° WIRE SIZE: 16-14HD AWG			
		APVD JL MECKLEY 31MAY96							
		PRODUCT SPEC							
		APPLICATION SPEC							
MATERIAL 		FINISH 		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
		WEIGHT		A2	00779	C=184269		—	
		CUSTOMER DRAWING		SCALE		10:1	SHEET	1 of 1	REV