BS14-M

Share

Loose Piece Splices

Butt Splice, non-insulated, 16 – 14 AWG wire range, bulk package.

Find A Distributor

Qty

Add to Bom

Specifications | Packaging Detail | Resources | Related Products

Top of Page



Specifications

Material	Copper
Finish/Coating	Tinned
Style	Butt Splice
Wire Range In. (mm^2)	16 - 14 AWG (1.5 - 2.5)
Barrel Configuration	Standard
Barrel Type	Brazed Seam
Base Material	Copper
Color Code	Metallic
Insulation Material	Non-Insulated
Plating Type	Tinned
Part Number Series	BS
Wire Strip Length In. (mm)	9/32" (7.1)
Flammability Rating	N/A
Maximum Output Voltage (V)	2000
CA-800/EZ Series Crimp Die	—
CA9 Series Crimp Die	—
CSA Certified	C22.2 No 65
UL Listed	UL 486C
Package Type	Box
Pieces Per Reel	—

Packaging Detail

UPC	07498383203
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	0.4190
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000

Resources

Selection Guides	Terminal Tools Selection Guide	English	View PDF (76.91KB) Download PDF Share PDF
Part Drawings	Butt Splice, Non- Insulated #22-10	English	View PDF (354.32KB) Download PDF Share PDF

Related Products

BS10-D

Butt Splice, non-insulated, 12 – 10 AWG wire range, bulk package.



BS10-L

Butt Splice, non-insulated, 12 – 10 AWG wire range, standard package.



BS14-C

Butt Splice, non-insulated, 16 – 14 AWG, standard package.

Copyright 2019 Panduit