This document was generated on 12/29/2022

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** 0150180594

**Status:** Active

**Overview:** FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers

**Description:** 0.50mm Pitch Premo-Flex FFC Jumper with Ears, Opposite Side Contacts (Type D), 203.00mm Cable Length, Gold (Au) Plating, 70 Circuits



*Series image - Reference only*

**Documents:**

Drawing (PDF)
Datasheet (PDF)
Product Specification 150180001-000 (PDF)
RoHS Certificate of Compliance (PDF)

**General**

| | |
|---|---|
| Product Family | Cable |
| Series | 15018 |
| Comments | Contacts on opposite sides, Type D |
| Crimp Quality Equipment | Yes |
| Overview | FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers |
| Product Name | Premo-Flex FFC Jumper |
| Taxonomy | Flexible Printed Circuit (FPC) |
| UPC | 193264451777 |

**Physical**

| | |
|---|---|
| Cable Length | 203.00mm |
| Circuits (Loaded) | 70 |
| Contact Layout Type | D (opposite side) |
| Material - Plating Mating | Gold |
| Packaging Type | Bag |
| Pitch - Mating Interface | 0.50mm |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | Flat Flex Cable |

**Electrical**

| | |
|---|---|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum | 60V AC |

**Material Info**

**Reference - Drawing Numbers**

| | |
|---|---|
| Product Specification | 150180001-000 |
| Sales Drawing | SD-15018-001-001 |

**EU ELV**
**Not Relevant**

**EU RoHS**
**Compliant**

**China RoHS**

**REACH SVHC**
Not Contained Per - ECHA_01_2020 (16 January 2020

**Halogen-Free Status**
**Not Low-Halogen**

For more information, please visit Contact US

| | |
|---|---|
| China ROHS | Green Image |
| ELV | Not Relevant |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**
15018 Series

**Mates With**
Easy-On FFC/FPC Connector 5051107091

This document was generated on 12/29/2022

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**