


环保物料

TEL:0769-82001899







SPECIFICATIONS

- 1.Voltage rating: 250V AC, DC
 - 2.Current rating: 7A, AC, DC
 - 3.Withstanding Voltage: 1500V AC/minute
 - 4.Insulation resistance:1000M Ω min
 - 5.Temperature range: -25 ° C-+85 ° C
 - 6.Contact resistance: 10m Ω max
- WAFER
Housing Material: LCP UL 94V0
Pin Material: Phosphor Bronze or Brass
Contact Area Plating: Plated Tin or Plated Gold
Mates with :P3960 series Housing
Poles:02-12P
Part No.: M3960RS-xx-LP-R

R=卷装 无=管装

Pin位数



PCB LAYOUT

编 号	尺寸 (mm)		
	A	B	C
02	3.96	9.90	11.88
03	7.92	13.86	15.84
04	11.88	17.82	19.80
05	15.84	21.78	23.76
06	19.80	25.74	27.72
07	23.76	29.70	31.68
08	27.72	33.66	35.64
09	31.68	37.62	39.60
10	35.64	41.58	43.56
11	39.60	45.54	47.52
12	43.56	49.50	51.48

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
				X.	±0.30 X° ±5°	CHKD				DATE	2010. 4. 12
				.X	±0.20 .X° ±2°	APPD		PRODUCT NAME	3.96mm Crimp Style Connectors	UNITS	mm
A0				.XX	±0.08 .XX° ±1°	VIEW				PART. NO.	M3960RS-xx-LP-R
VER	MODIFICATION		DRAW	DATE	.XXX ±0.03 .XXX° ±0.5°			DWG NO.	009		
1		2		3		4		5		6	
7		8		9		10					