





A B C D E F



修 订	标 记	修 改 描 要	签 名	日 期
REV NO		REVISION DESCRIPTION	SIGNATURE	DATE
		NEW DWG		2016-03-12




序号 (NO.)	品名 (Name)	材质 (Material)
①	0.5后锁胶芯(H=2.0) 0.5 PH Backflip Type Housing (H=2.0)	LCP UL94V-0 本色 <b>Natural</b>
②	0.5后锁端子(H=2.0) 0.5 PH Backflip Type Terminal (H=2.0)	磷青铜/表面镀金 Phosphor Bronze/ Gold Plating
③	0.5后锁后盖(H=2.0) 0.5 PH Backflip Type Actuator (H=2.0)	LCP UL94V-0 黑色 <b>Black</b>
④	0.5后锁焊片(H=2.0) 0.5 PH Backflip Type Fitting Nail (H=2.0)	磷青铜/表面镀锡 Phosphor Bronze/ Tin Plating



CKT	A			B			C			
	A	B	C	CKT	A	B	C	A	B	C
4	1.5	2.56	5.5	33	16.0	17.06	20.0			
5	2.0	3.06	6.0	34	16.5	17.56	20.5			
6	2.5	3.56	6.5	35	17.0	18.06	21.0			
7	3.0	4.06	7.0	36	17.5	18.56	21.5			
8	3.5	4.56	7.5	37	18.0	19.06	22.0			
9	4.0	5.06	8.0	38	18.5	19.56	22.5			
10	4.5	5.56	8.5	39	19.0	20.06	23.0			
11	5.0	6.06	9.0	40	19.5	20.56	23.5			
12	5.5	6.56	9.5	41	20.0	21.06	24.0			
13	6.0	7.06	10.0	42	20.5	21.56	24.5			
14	6.5	7.56	10.5	43	21.0	22.06	25.0			
15	7.0	8.06	11.0	44	21.5	22.56	25.5			
16	7.5	8.56	11.5	45	22.0	23.06	26.0			
17	8.0	9.06	12.0	46	22.5	23.56	26.5			
18	8.5	9.56	12.5	47	23.0	24.06	27.0			
19	9.0	10.06	13.0	48	23.5	24.56	27.5			
20	9.5	10.56	13.5	49	24.0	25.06	28.0			
21	10.0	11.06	14.0	50	24.5	25.56	28.5			
22	10.5	11.56	14.5	51	25.0	26.06	29.0			
23	11.0	12.06	15.0	52	25.5	26.56	29.5			
24	11.5	12.56	15.5	53	26.0	27.06	30.0			
25	12.0	13.06	16.0	54	26.5	27.56	30.5			
26	12.5	13.56	16.5	55	27.0	28.06	31.0			
27	13.0	14.06	17.0	56	27.5	28.56	31.5			
28	13.5	14.56	17.5	57	28.0	29.06	32.0			
29	14.0	15.06	18.0	58	28.5	29.56	32.5			
30	14.5	15.56	18.5	59	29.0	30.06	33.0			
31	15.0	16.06	19.0	60	29.5	30.56	33.5			
32	15.5	16.56	19.5	80	39.5	40.56	43.5			



适用扁平线 (Applicable Flat Cable)



适用线路板 (PCB LAYOUT)

- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
  2. 温度范围(Temperature range): -40° C~+85° C.
  3. 额定电压(Rated voltage): 50V, AC/DC(=等效).
  4. 接触电阻(Contact resistance): ≤0.03 Ω.
  5. 绝缘电阻(Insulation resistance): ≥500M Ω
  6. 产品料号(Product material No.):



**深圳市华德共创科技有限公司**  
Shenzhen Huade co-create Technology Co., LTD  
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			TITLE: 产品名称: 0.5间距2.0高前插后掀盖式			
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: 0.5K-DHXX-nPWB			
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001

A B C D E F