



SPECIFICATION:

Current Rating:3.0A AC/DC
Voltage rating: 250V AC/DC
Contact Resistance:20m Ω (max)
Insulation Resistance:1000M Ω Min at 500V DC
Dielectric Strength:500V AC Per 1 Minute
Operating Temperature:-40℃ TO +105℃

MATERIALS:

Insulator: PA6T UL94V-0
Contact:Brass
Contact plated: Gold Over Nickel

Poles	Part No.	Dimension mm			
		A	B	C	D
6	B-3100S06P-A110	26.94	5.08	/	/
8	B-3100S08P-A110	29.48	7.62	/	/
10	B-3100S10P-A110	32.02	10.16	/	/
12	B-3100S12P-A110	34.56	12.70	/	/
14	B-3100S14P-A110	37.10	15.24	/	/
16	B-3100S16P-A110	39.64	17.78	/	/
18	B-3100S18P-A110	42.18	20.32	/	/
20	B-3100S20P-A110	44.72	22.86	10.49	7.39
24	B-3100S24P-A110	49.80	27.94	13.03	9.93
26	B-3100S26P-A110	52.34	30.48	14.30	11.20
28	B-3100S28P-A110	54.88	33.02	15.57	12.47
30	B-3100S30P-A110	57.42	35.56	16.84	13.74
34	B-3100S34P-A110	62.50	40.64	19.38	16.28
40	B-3100S40P-A110	70.12	48.26	23.19	20.09
44	B-3100S44P-A110	75.20	53.34	25.73	22.63
50	B-3100S50P-A110	82.82	60.96	29.54	26.44
60	B-3100S60P-A110	95.52	73.66	33.89	32.79
64	B-3100S64P-A110	100.60	78.74	38.43	35.33

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 310S-XP PA6T 镀金 (2.54直牛角)			
DRAWN: LYF	DATE: 2024-04-07	PART. NO.		B-3100SXXP-A110	
		UNIT	mm	SCALE	free
		FILE NO.		Ckmtw-310-00015	REV. A