


















INITIAL REVISION:		
DRWN	SHSHIBATA	2007/12/18
CHECK	HKOMATSU	2007/12/18
APPR	AKANESHIGE	2007/12/18

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
$\nabla_A = 0$		DIMENSION UNITS		SCALE		CURRENT REV DESC: For fixing wrong view of 6kct				molex									
$\nabla_G = 0$		mm		4:1															
$\nabla_E = 0$		GENERAL TOLERANCES (UNLESS SPECIFIED)								2.0MM PITCH W/B CONN. WAFER ASSY R/A SMT									
		ANGULAR TOL ± 0.5°																	
DIVISIONAL SYMBOLS		4 PLACES		±		STATUS: Production DRWN: Hideo Yoneyama 2024-05-14 CHK'D: Hironichi Komatsu 2024-05-16 APPR: Takashi Iida 2024-05-16				PRODUCT SALES DRAWING									
		3 PLACES		±															
		2 PLACES		±															
		1 PLACE		±															
		0 PLACES		±															
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
								A3-SIZE		502352		SEE CHART		GENERAL MARKET		3 OF 4			
												DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
												SD-502352-001		PSD		001		L4	

10		9		8		7		6		5		4		3		2		1		
F	Sn NATURAL	34.0	502352-1500		15		Au NATURAL	34.0	502352-1510		15									
		32.0	502352-1400		14			32.0	502352-1410		14									
		30.0	502352-1300		13			30.0	502352-1310		13									
		28.0	502352-1200		12			28.0	502352-1210		12									
		26.0	502352-1100		11			26.0	502352-1110		11									
		24.0	502352-1000		10			24.0	502352-1010		10									
		22.0	502352-0900		9			22.0	502352-0910		9									
		20.0	502352-0800		8			20.0	502352-0810		8									
		18.0	502352-0700		7			18.0	502352-0710		7									
		16.0	502352-0600		6			16.0	502352-0610		6									
		14.0	502352-0500		5			14.0	502352-0510		5									
		12.0	502352-0400		4			12.0	502352-0410		4									
10.0	502352-0300		3		10.0	502352-0310		3												
8.0	502352-0200		2		8.0	502352-0210		2												
PLATING COLOR	A	EMBOSSED PACKAGE ORDER NO.		CKTS		PLATING COLOR	A	EMBOSSED PACKAGE ORDER NO.		CKTS										
CONNECTOR SERIES NO. 502352-**08						CONNECTOR SERIES NO. 502352-**18														
D	Sn BLACK	34.0	502352-1501		15		Sn RED	-	-		15		Sn BLUE	-	-		15			
		32.0	502352-1401		14			-	-		14			-	-		14			
		30.0	502352-1301		13			-	-		13			-	-		13			
		28.0	502352-1201		12			-	-		12			-	-		12			
		26.0	502352-1101		11			-	-		11			-	-		11			
		24.0	502352-1001		10			-	-		10			-	-		10			
		22.0	502352-0901		9			-	-		9			-	-		9			
		20.0	502352-0801		8			20.0	502352-0802		8			20.0	502352-0803		8			
		18.0	502352-0701		7			-	-		7			-	-		7			
		16.0	502352-0601		6			16.0	502352-0602		6			16.0	502352-0603		6			
		14.0	502352-0501		5			-	-		5			-	-		5			
		12.0	502352-0401		4			12.0	502352-0402		4			12.0	502352-0403		4			
10.0	502352-0301		3		10.0	502352-0302		3		10.0	502352-0303		3							
8.0	502352-0201		2		8.0	502352-0202		2		8.0	502352-0203		2							
PLATING COLOR	A	EMBOSSED PACKAGE ORDER NO.		CKTS		PLATING COLOR	A	EMBOSSED PACKAGE ORDER NO.		CKTS		PLATING COLOR	A	EMBOSSED PACKAGE ORDER NO.		CKTS				
CONNECTOR SERIES NO. 502352-**28						CONNECTOR SERIES NO. 502352-**48						CONNECTOR SERIES NO. 502352-**68								
</																				

注記
NOTES

1. 製品番号

ナチュラル・錫めっき: 502352-**00

ナチュラル・金めっき: 502352-**10

黒・錫めっき: 502352-**01

赤・錫めっき: 502352-**02

青・錫めっき: 502352-**03

詳細寸法については、製品単体図面を参照下さい。

PART NO.

NATURAL Sn Plating: 502352-**00

NATURAL Au Plating: 502352-**10

BLACK Sn Plating: 502352-**01

RED Sn Plating: 502352-**02

BLUE Sn Plating: 502352-**03


SEE SALES DRAWING FOR CONNECTOR

2. 梱包数量: 700個/リール

NUMBER OF CONNECTORS 700PCS/REEL

3. リードテープ長さ

LEAD TAPE LENGHT



4. 材料

MATERIAL

キャリアテープ: ポリスチレン

CARRIER TAPE: POLYSTYRENE

トップテープ: PET, PE, PEF

TOP TAPE: PET, PE, PEF

リール: ポリスチレン

REEL: POLYSTYRENE

5. 一般公差

GENERAL TOLERANCES

10 UNDER: ±0.2

10 OVER 30 UNDER: ±0.25

30 OVER: ±0.3

ANGULAR: ±1°

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:					
mm		NTS						molex	
GENERAL TOLERANCES (UNLESS SPECIFIED)									
ANGULAR TOL		±	°						
4 PLACES		±							
3 PLACES		±							
2 PLACES		±							
1 PLACE		±							
0 PLACES		±							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES	
								A3-SIZE 502352	
				</					

		9				8		7				6		5		4		3		2		1											
Sn NATURAL	52.4	61.4	57.4	56	26.2	34.3	502352-1500		15	Au NATURAL	52.4	61.4	57.4	56	26.2	34.3	502352-1510		15														
						32.3	502352-1400		14							32.3	502352-1410		14														
						40.4	49.4	45.4	44							20.2	30.3	502352-1300						13	40.4	49.4	45.4	44	20.2	30.3	502352-1310		13
																	28.3	502352-1200						12						28.3	502352-1210		12
																	26.3	502352-1100						11						26.3	502352-1110		11
																	24.3	502352-1000						10						24.3	502352-1010		10
																	22.3	502352-0900						9						22.3	502352-0910		9
						28.4	37.4	33.4	32							14.2	20.3	502352-0800						8	28.4	37.4	33.4	32	14.2	20.3	502352-0810		8
																	18.3	502352-0700						7						18.3	502352-0710		7
																	16.3	502352-0600						6						16.3	502352-0610		6
						/	29.4	25.4	24							11.5	14.3	502352-0500						5	/	29.4	25.4	24	11.5	14.3	502352-0510		5
																	12.3	502352-0400						4						12.3	502352-0410		4
																	10.3	502352-0300						3						10.3	502352-0310		3
8.3	502352-0200		2	8.3	502352-0210					2																							
PLATING COLOR	F	E	D	C	(B)	(A)	エンボス梱包品 製品番号 EMBOSSED PACKAGE MATERIAL NO.		極数 CKT.	PLATING COLOR	F	E	D	C	(B)	(A)	エンボス梱包品 製品番号 EMBOSSED PACKAGE MATERIAL NO.		極数 CKT.														

Sn BLACK	52.4	61.4	57.4	56	26.2	34.3	502352-1501	15	Sn RED								15	Sn BLUE											15	
						32.3	502352-1401	14											14										14	
	40.4	49.4	45.4	44	20.2	30.3	502352-1301	13											13										13	
						28.3	502352-1201	12														12								12
						26.3	502352-1101	11														11								11
						24.3	502352-1001	10														10								10
						22.3	502352-0901	9														9								9
	28.4	37.4	33.4	32	14.2	20.3	502352-0801	8											8										8	
						18.3	502352-0701	7														7								7
						16.3	502352-0601	6														6								6
					11.5	14.3	502352-0501	5											5										5	
						12.3	502352-0401	4													4								4	
						10.3	502352-0301	3													3								3	
8.3						502352-0201	2											2								2				
PLATING COLOR	F	E	D	C	(B)	(A)	エンボス梱包品 製品番号 EMBOSSED PACKAGE MATERIAL NO.	極数 CKT.	PLATING COLOR	F	E	D	C	(B)	(A)	エンボス梱包品 製品番号 EMBOSSED PACKAGE MATERIAL NO.	極数 CKT.	PLATING COLOR	F	E	D	C	(B)	(A)	エンボス梱包品 製品番号 EMBOSSED PACKAGE MATERIAL NO.	極数 CKT.				