




RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)



SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature:-40°to+105°
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
ZX-PM2.0-2-1PY	2*1	0.00	2.00
ZX-PM2.0-2-2PY	2*2	2.00	4.00
ZX-PM2.0-2-3PY	2*3	4.00	6.00
ZX-PM2.0-2-4PY	2*4	6.00	8.00
ZX-PM2.0-2-5PY	2*5	8.00	10.00
ZX-PM2.0-2-6PY	2*6	10.00	12.00
ZX-PM2.0-2-7PY	2*7	12.00	14.00
ZX-PM2.0-2-8PY	2*8	14.00	16.00
ZX-PM2.0-2-9PY	2*9	16.00	18.00
.....			
ZX-PM2.0-2-40PY	2*40	(PIN-1)x2.0	(PIN)x2.0

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE		料号 PART NO.	ZX-PM2.0-2-NPY		版本 REV.	A
			X.	±0.5	X.*	±5°	审核 CHECK	LEO	品名 TITLE	2.0FH H6.35 2xnPin 180度 Y型 PC2.8 6T	页次 SHEET	1/1
			X.X	±0.2	X.X*	±2°	核准 APPROVAL	JOHN	客户料号 CUTM.NO.			
			X.XX	±0.1	X.XX*	±1°	单位 UNITS	MM	比例 SCALE	1:1	兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.	