










版数 REV.	年月日 DATE	図 NO.	変更内容 DESCRIPTION	製 図 DR.	担 当 CHK.	査 閲 APPD.	承認 APPD.
3	29/JUN/2012	002873	REDRAWN	T. ENOMOTO	Y. WATANABE	—	A. OONO

WISDOM承認 2012/06/29



- NOTE1. FEMALE-COUNTERPART CONNECTOR : MX34024SF1 (SJ100271)
2. APPLICABLE SCREW : JIS B 1122 CROSS RECESSED HEAD TAPPING SCREW M3×6, CLASS 2 (TYPE B)
- 注 1. かん合相手メスコネクタ : MX34024SF1 (SJ100271)
2. 推奨取付ネジ JIS B 1122 十字穴付なベタッピンネジ 2種 M3×6

3	TERMINAL-L2	12	BRASS	PLATING: Sn	MATERIAL-PLATING
2	TERMINAL-L1	12	BRASS	PLATING: Sn	MATERIAL-PLATING
1	HOUSING	1	SPS-GF30		COLOR: GRAY
符号 NO.	名 称 DESCRIPTION	個 数 QTY.	材 料 MATERIAL	仕 上 FINISH	備 考 REMARKS
仕様書 (SPECIFICATION)		第1版 (ORIGINAL DATE)		尺度 (SCALE)	シリーズ (SERIES)
JACS-1754 JABL-1754		18/NOV/2003		2:1	MX34
一般公差 (GENERAL TOLERANCE)		製図 DR.		日本航空電子工業株式会社	
		J. ICHIYAMA		JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.	
寸法 (DIMENSION)		担当 CHK.		図面番号 (DRAWING NO.)	
		N. TOUDOU		SJ100269	
角度 (ANGLES)		査閲 APPD.		質量 (MASS)	
		—		6.5g	
. ±0.8		承認 APPD.		図面番号 (DRAWING NO.)	
. × ±0.4		T. TOTANI		SJ100269	
. × × ±0.1					
. × × × ±					