

End plate, Width: 1.5 mm, Colour: Grey

RAL: Ähnlich 7035

Business data

Article number	<u>27119.6</u>
Article name	PAPIKD 2,5 GR
GTIN (EAN)	4044211227340
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	5.2 g
Weight per piece (including packaging)	5.4 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	27119.6
Product description	End plate

Technical data

Dimensions

Length	102 mm
Width	1.5 mm
Height	56.2 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	120 °C


Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media


Accessories

##INVERSE##CONTA-CONNECT



Three-level initiator terminal | Multi-wire terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5,1 mm, Colour: Grey


Article number	Article name	GTIN (EAN)	Packaging unit
<u>27039.6</u>	PIKD 2,5 GR	4044211227210	50



Three-level initiator terminal | Multi-wire terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27041.6</u>	PIKD 2,5/SV GR	4044211227241	50

##INVERSE##CONTA-CONNECT



Three-level initiator terminal | Multi-wire terminal, Push-in connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27041.6</u>	PIKD 2,5/SV GR	4044211227241	50