








客选	高度	PCS/盘
	H=0.55mm	5000

客选	按力规格 A
	100^{+40}_{-20}gf
	160^{+40}_{-20}gf
	250^{+40}_{-20}gf
	300^{+40}_{-20}gf







PCB板焊盘尺寸

电路图

NO.	NAME	MATERIAL	FINISHING
1	TERMINAL	phosphorous bronze	Silver plating
2	CASE	LCP	White
3	CONTACT	SUS301	Silver plating
4	Waterproof membrane	PI	Yellow

SPECIFICATIONS	
Operating temperature rangs	-30° to +85°
Rating	DC 12V 50mA Max.
Lifetime	50000 Cycles min
Contact Resistance	100mΩ Max
Dielectric strength	250V AC for 1min.
Travel	0.15±0.1mm
Solder temperature	255±5°

THIS DOCUMENT IS THE SOLE PROPERTY OF LIBANG ELECTRONICS TECHNOLOGY AND SHOULD NOT BE USED IN WHOLE OR IN PART WITHOUT PRIOR WRITTEN PERMISSION.

深圳市逸致电子有限公司
Shenzhen Yizhi Electronics Co., LTD

.X: ±0.20 X°: ±8°
.XX: ±0.10 .X°: ±5°
.XXX: ±0.05 .XX°: ±2°

PART NO.: YZA-065

APPD.		PART NO.: *PART_NO*	
CHKD.	*CHECK*	DRW. NO.: *DRW_NO*	
DR.	*DRAW*	FINISH: ---	MAT'L.: ---
		SCALE: *1:1*	REV.: *A0* UNIT: *MM* PAGE: *1—1*