








PCB LAYOUT



▲ CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. RATING: 12VDC @ 50mA
4. CONTACT RESISTANCE: 100m Ω MAX.
5. INSULATION RESISTANCE: 100M Ω MIN @ 500VDC
- ▲ 6. OPERATING FORCE: 450 $\pm$ 150gf
7. TRAVEL: 0.45 $\pm$ 0.15mm
8. OPERATING TEMPERATURE: -40°C to 85°C
9. OPERATING LIFE: 500,000 CYCLES
- ▲ 10. LED COLOR: NO LED
11. IP67 RATED
12. ▲ DENOTES CRITICAL PARAMETERS



TITLE TL6215VF450NGK

A	24241	New Release	3/31/20	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 4:1	DATE 3/31/2020	DR MW	DWG B200634	REV A
--------------	-------------------	----------	----------------	----------