

1


2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	

16.20 [0.638]



10.50 [0.413]

规格 Specification:

1.额定值 Rating:3A 125/250VAC

2.接触电阻 Contact resistance:≤30 mΩ

3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)

4.电气寿命 Electronics life:>10000 cycles

5.操作力 Operation force:500±150gf

6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 03 12 S G-XX N 2 X X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① SS: 立式拨柄开关;

② X: A: 金属外壳;

BLANK: 塑胶外壳;

③ 03: 额定值3A;

④ 12: 单排两档;

⑤ S: 焊线端子;

⑥ G: 弧形拨柄;

⑦ XX: 拨柄高度H: 3~15mm;

⑧ N: 方形外壳;

⑨ 1: 端子焊脚规格TYPE-1; 2: 端子焊脚规格TYPE-2;

3: 端子焊脚规格TYPE-3; 4: 端子焊脚规格TYPE-4;

5: 端子焊脚规格TYPE-5;

⑩ X: 拨柄颜色: B-黑色; W-白色; R-红色

⑪ X: 主体颜色: B-黑色; W-白色; R-红色

A

A

B

B

C

C


D

D

5.50 [0.217]


4.00 [0.157] Travel

3.30 [0.130]



产品凸码标识

8.50 [0.335]




4.00 [0.157]


XKB **US**

SS Series
3A 125/250VAC

产品字码标识



CIRCUIT



ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB

DESIGN
CHECKED
APPROVED

桑 葚

VIEW:

UNIT: mm/in

SIZE: A4

MODEL TYPE:
SLIDE SWITCHPART NO.:
SS-0312SG-XXN2BB

DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A0

1

2

3

4