

标 记

MARK

ECN编号/变更内容

ECN NO/DEFINITION

修 改

REVISE

日 期

DATE

核 准

APPROVE

A

B

C

D

E

F

G

A

B



C

D

E

F

G



SPECIFICATION (技术要求)

1. Operating Temperature (环境温度): $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$
2. Voltage Rating (额定电压): 50V AC/DC
3. Current Rating (额定电流): 0.5A
4. Contact Resistance (接触电阻): $30\text{m}\Omega$
5. Insulation Resistance (绝缘电阻): $100\text{M}\Omega$
6. Dielectric Withstanding Voltage (耐电压): 500V AC Min
7. Insertion/Withdrawal Force (插拔力): 3-50N
8. Life Time (mating cycles) 寿命: >1000 Cycles
9. SIGNAL LOSS $<1\text{dB}$ IN BOTH VHF, UHF BAND.
10. NOMINAL IMPEDANCE : 75 OHMS.
11. OPERATING FREQUENCY : 0-2 GHZ.

3	F头	锌合金	镀镍	
2	支架	SPCC	— —	
1	绝缘体	PPS	棕色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司


品 名	屏蔽罩
TITLE	
料 号	HC-PBZ-R1365
PART NO	

GENERAL TOLERANCES
(UNLESS SPECIFIED)

比 列

SCALE

1:1



$L \leq 4$ ± 0.2
 $4 < L \leq 16$ ± 0.3
 $16 < L \leq 63$ ± 0.4
 $63 < L$ ± 0.5
ANGLE $\pm 3^{\circ}$

单 位

MM

制 图

AhYe



张 数

1 OF 1

审 核

夏操云

版 本

A

批 准

赵亮亮