
Glenair®


557-071
D-Subminiature Solid Banding Backshell with Qwik-Ty® and Slot Options

557 T 071 M 2 31 S C T B -32


- Basic Part No.
- Cable Entry Style
  - T = Top
  - S = Side
  - B = 45°
- Basic Part Number
- Finish Symbol (Page 3)
- Shell Size (Table I)
- Dash No. (Table II)
- Slot (Omit for None)
- Optional Retainer (Omit for Standard)
- Qwik-Ty Option (Omit for None)
- B = Band Supplied (600-052), Omit for None. (Note: Band 600-057 Supplied If -32 Option)
- -32 = Band Platform Length of .32 and M Dia (Omit for Standard .50 Length)





Qwik-Ty® Option




Slot Option









© 2011 Glenair, Inc.

557-071
D-Subminiature Solid Banding Backshell with Qwik-Ty® and Slot Options

TABLE I: SHELL SIZE & BACKSHELL DIMENSIONS

Shell Size	A Max	B	C	D ±.005 (.1)	E	J
1	1.25 (31.8)	.53 (13.5)	1.50 (38.1)	.984 (25.0)	1.25 (31.8)	1.68 (42.7)
2	1.58 (40.1)	.53 (13.5)	1.50 (38.1)	1.312 (33.3)	1.25 (31.8)	1.68 (42.7)
3	2.13 (54.1)	.53 (13.5)	1.50 (38.1)	1.852 (47.0)	1.25 (31.8)	1.68 (42.7)
4	2.77 (70.4)	.53 (13.5)	1.50 (38.1)	2.500 (63.5)	1.25 (31.8)	1.68 (42.7)
5	2.68 (68.1)	.66 (16.8)	1.50 (38.1)	2.406 (61.1)	1.38 (35.1)	1.81 (46.0)


TABLE II: CABLE ENTRY

Dash No.	F Dia	G Dia	H Dia	K Dim	L Dim	M Dia **
16	.175 (4.4)	.300 (7.6)	.412 (10.5)	.08 (2.0)	.19 (4.8)	.362 (9.2)
23	.250 (6.4)	.375 (9.5)	.487 (12.4)	.08 (2.0)	.22 (5.6)	.437 (11.1)
30	.312 (7.9)	.437 (11.1)	.550 (14.0)	.08 (2.0)	.25 (6.4)	.500 (12.7)
31	.375 (9.5)	.500 (12.7)	.612 (15.5)	.08 (2.0)	.28 (7.1)	.562 (14.3)
32	.430 (10.9)	.555 (14.1)	.667 (16.9)	.08 (2.0)	.31 (7.9)	.617 (15.7)
33*	.550 (14.0)	.675 (17.1)	.787 (20.0)	.08 (2.0)	.38 (9.7)	.737 (18.7)


* Available in Shell Size 5 only.

** Dia with -32 optional band platform length.

1. Metric dimensions (mm) are indicated in parentheses.
2. **DO NOT USE CONNECTORS WITH FLOAT.**



STANDARD HARDWARE SUPPLIED
2 Socket Head Jackscrews with "E" rings (Ref. MS16633-4011) supplied unassembled.
Glenair part number 687-172



"C" OPTION HARDWARE
Glenair part number 687-236

© 2011 Glenair, Inc.