# Eaton 170M4831

Fuse-link, high speed, 125 A, AC 1000 V, size 00, 30 x 47 x 98 mm, aR, DIN, IEC, single indicator

| □□□□ | |
|---|---|
| **PRODUCT NAME** | Eaton Bussmann series high speed square body fuse |
| **CATALOG NUMBER** | 170M4831 |
| **UPC** | 051712556040 |
| **PRODUCT LENGTH/DEPTH** | 233 mm |
| **PRODUCT HEIGHT** | 66 mm |
| **PRODUCT WIDTH** | 140 mm |
| **PRODUCT WEIGHT** | 234.8333333 g |
| **COMPLIANCES** | CE Marked<br>RoHS Compliant |
| **CERTIFICATIONS** | IEC Rated<br>UL Recognized |

Powering Business Worldwide

| □□□□ | |
|---|---|
| **AMPERAGE RATING** | 125 A |
| **BREAKING CAPACITY** | 125 kA |
| **FUSE INDICATOR** | Top fuse status indicator |
| **INSULATED METAL GRIPPING LUGS (IMGL)** | No |
| **UTILIZATION CATEGORY** | aR (accompanied semiconductor protection) |
| **VOLTAGE TYPE** | AC |
| **FUSE SIZE** | 00 |
| **RATED VOLTAGE AC** | 1000 V |
| **CENTER-TO-CENTER DISTANCE OF CONNECTIONS** | 78 mm |
| **CURRENT TYPE** | AC |
| **MOUNTING DIMENSION** | M10 |
| **CLASS** | Class aR |
| **CLEARING (I2T)** | 11500 at 1000 V |
| **WATT LOSSES** | 33 W |
| **FUSE SHAPE** | Square body, slotted center bolted tags |
| **PRE ARC (I2T)** | 1500 |
| **COLOR** | None |
| **INTERRUPT RATING** | 125 kAIC |
| **CONNECTION** | Blade end x Din 43-620 blade end |
| **CONSTRUCTION SIZE** | 00 |
| **PACKAGING TYPE** | Standard |
| **VOLTAGE RATING** | 1000 V (IEC) |
| **TYPE** | Fuse |
| **APPLICATION** | Semiconductor, DC Common bus, DC drives, power converters/rectifiers |
| **FUSE TYPE** | DIN 43653<br>00TN/80 Type T Indicator for micro<br>Bolted tag |
| **FUSE SYSTEM (ACCORDING TO IEC 60269)** | Other |

| □□ | |
|---|---|
| DECLARATIONS OF CONFORMITY | eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251013en.pdf |

| | |
|---|---|
| □□□□: | |
| □□□□: | |
| □□□: | |
| □□: | |

□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2026 □□ □□□□□□□□

□□□□□□□□□□□□□□□□□□□□□□□□□□□□□□