





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		C1	REVISED PER ECR-10-013120	24JUN10	HMR	GJ

- 1 SPECIFICATIONS:
MAGNET WIRE #18- #34 AWG. 1.02[.040]-0.16[.006] DIA COPPER,
OTHER SIZES MAY BE ACCOMMODATED, CONSULT TYCO ELECTRONICS
FOR APPROVAL.
- 2 POCKET RECOMMENDATION: # 1601427
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS
SPECIFICATION 114-13166 FIGURE 15.
- 4 TWO(2) TERMINALS SHOWN FOR ILLUSTRATION PURPOSES ONLY.



—		—		—	
—		—		—	
—		—		—	
UNPLATED		031-023-000		4-1601011-1	
POST PLATED TIN OVER NICKEL		—		1601011-2	
UNPLATED		131-023-000		1601011-1	
FINISH		REFERENCE PART NUMBER		TE PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.WELLER 11JAN2002		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK M.FEHER 11JAN2002			
		APVD K.RANDOLPH 11JAN2002			
		PRODUCT SPEC 108-2085			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME STANDARD RANGE WIRE TO 4.75 X 0.51 BARB TAB SIAMEZE TERMINAL	
		0 PLC ± -		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
		1 PLC ± -			
		2 PLC ± 0.13[.005]			
		3 PLC ± -			
4 PLC ± -		APPLICATION SPEC 3			
ANGLES ± 2°					
MATERIAL BRASS, SPRING HARD		FINISH SEE TABLE		WEIGHT —	
		CUSTOMER DRAWING		A2 00779 C-1601011	
		SCALE 9:1		SHEET 1 of 1	
		REV C1			