


WWW.XYECONN.COM

REV.	Q'TY	ECN. NO.	APR.	DATE










[Schematic]



[P.C.B.LAYOUT]

NOTES:

1.Specification:

1>.Operation force: 1000gf Max.

2>.Operation Temperature: -30℃ to +85℃.

3>.Storage Temperature: -40℃ to +85℃.

4>.Mechanical Life: 3000 cycles operations.

5>.Resistance to Soldering: 260±5℃ for 3-5 Seconds.

2.PLATING:

1>.GOLD flash 1u"(min) SOLDERTAIL,

3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

1>.Non-switch Rating:100mA at 50V DC.

2>.Switching Rating: 25mA at 24V DC.

3>.Contact Resistance: Inital 50mΩ Max.

Contact Resistance: After life 100mΩ Max.

4>.Insulation Resistance:100MΩ Min at 500VDC.

5>.Dielectric Strength: 500V AC for 60seconds.

6>.Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

XY-DSIC XX L S- R

(包装方式:T=Tub R=Reel)

(端脚型:S=贴片 / D=插件 / J型)

(L=高桥 / S=低桥 / T=低桥贴胶)

(开关位数: 02位-----12位)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd		
TOLERANCE UNLESS OTHERWISE SPECIFIED				
.X±0.35	X.°± 5°	APR. Alex	TITLE: PRODUCT Family DSIC Series Pitch 2.54mm	
.XX±0.25	.X°± 3°	CHK. Jack	DWG NO. XY-DSIC08LS-R	
.XXX±0.15	.XX°± 1°	DRA. Can	PROJ.	CUSTOMER DRAWING
			SIZE A4 / SCALE 1:1	SHEET 1/1 / REV. A

F-RD-18A