





SPECIFICATIONS
Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240° C for 30-60 seconds
(260° C for 5 seconds)

P/N	PIN	DIM. A	DIM. B
HMT-PM254-1*01W-H85	1	0.00	2.54
HMT-PM254-1*02W-H85	2	2.54	5.08
HMT-PM254-1*03W-H85	3	5.08	7.62
HMT-PM254-1*04W-H85	4	7.62	10.16
HMT-PM254-1*05W-H85	5	10.16	12.70
HMT-PM254-1*06W-H85	6	12.70	15.24
HMT-PM254-1*07W-H85	7	15.24	17.78
HMT-PM254-1*08W-H85	8	17.78	20.32
HMT-PM254-1*09W-H85	9	20.32	22.86
.....			
HMT-PM254-1*40W-H85	40	(PIN-1) X 2.54	(PIN) X 2.54

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd		
X.±0.30	X.°±5°	PART NO.	TITLE: 2.54FH H8.5 1x40Pin 90° Y型 PC3.2 PB10.2 6T	
.X±0.20	.X°±1°	HMT-PM254-1*NW-H85	CUSTOMER	SIZE
.XX±0.10	.XX°±0.5°	DESIGN: James		UNITS
MANUFACTURE DWG		CHED: Talen		SCALE
		APPD: Sophia		SHEET
				N:A 1/1