

Specification Sheet

Part Number: 151-00180



HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.

An assortment of Connector Cips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Conn. Clip w/Oval Fir Tree, 0.6-6.0 mm Panel Thick, 6.2x12.2 mm Hole Dia, PA66HIRHS, Black, 1000/pkg

Article Number	151-00180
Type	YCCFT62x122
Quantity Per	pcs.
Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
Short Description	Conn. Clip w/Oval Fir Tree, 0.6-6.0 mm Panel Thick, 6.2x12.2 mm Hole Dia, PA66HIRHS, Black, 1000/pkg
Global Part Name	YCCFT62x122-PA66HIRHS

Length L (Imperial)	0.83
Length L (Metric)	21.08
Fixation Method	Fir Tree for oval holes
Width W (Imperial)	0.63
Width W (Metric)	16.0
Height H (Imperial)	0.71
Height H (Metric)	18.0
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.24
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.24 x 0.48
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm
Mounting Hole Diameter D Min (Imperial)	0.244
Mounting Hole Diameter D Max (Imperial)	0.48
Mounting Hole Diameter D Max (Metric)	12.2

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).