



Part Number : [193230015](#)
Product Description : VersaKrimp Metric Ring
Terminal for M8 Stud Size (5/16"), Un-insulated, Carton
Series Number : 19323
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : C6-330-M8



Documents and Resources

Drawings

[193230015 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19323
Description	VersaKrimp Metric Ring Terminal for M8 Stud Size (5/16"), Un-insulated, Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Metric Ring Terminal
UPC	887191289991

Agency

UL	E32244
----	--------

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Net Weight	1.791/g
Packaging Type	Carton
Stud Size	M8
Wire Size (AWG)	N/A
Wire Size mm ²	2.50-6.00

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm ² - 0.5mm ²	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>