


A-A SECTION



RECOMMEND P. C. B LAYOUT  
PCB TOLERANCE: ±0.05 (TOP VIEW)

SPECIFICATIONS

Current Rating: 1.0 Amps  
 Withstanding Voltage: AC 500V  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Operation Temperature: -40° to +105°  
 Insulator Material: Polyester (UL94V-0)  
 Contact Material: Brass  
 Standard: PA6T  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240° C for 30-60 seconds  
 (260° C for 5 seconds)

| No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| —      | —      | —      | 22     | 12.70  | 13.97  | 42     | 25.40  | 26.67  |
| —      | —      | —      | 24     | 13.97  | 15.24  | 44     | 26.67  | 27.94  |
| 6      | 2.54   | 3.81   | 26     | 15.24  | 16.51  | 46     | 27.94  | 29.21  |
| 8      | 3.81   | 5.08   | 28     | 16.51  | 17.78  | 48     | 29.21  | 30.48  |
| 10     | 5.08   | 6.35   | 30     | 17.78  | 19.05  | 50     | 30.48  | 31.75  |
| 12     | 6.35   | 7.62   | 32     | 19.05  | 20.32  | 52     | 31.75  | 33.02  |
| 14     | 7.62   | 8.89   | 34     | 20.32  | 21.59  | 54     | 33.02  | 34.29  |
| 16     | 8.89   | 10.16  | 36     | 21.59  | 22.86  | 56     | 34.29  | 35.56  |
| 18     | 10.16  | 11.43  | 38     | 22.86  | 24.13  | 58     | 35.56  | 36.83  |
| 20     | 11.43  | 12.70  | 40     | 24.13  | 25.40  | 60     | 36.83  | 38.10  |

 深圳市韩下电子有限公司

|                                      |         |       |         |                                   |    |                        |                          |           |
|--------------------------------------|---------|-------|---------|-----------------------------------|----|------------------------|--------------------------|-----------|
| UNLESS OTHERWISE SPECIFIED TOLERANCE |         |       |         | DRAWN NAME: HX JN1.27-2x4 TP H4.9 |    |                        |                          |           |
| X                                    | : ±0.30 | X°    | : ±5°   | SIZE                              | A4 | SCALE                  | N:1                      | PROCT NO. |
| X.X                                  | : ±0.25 | X.X°  | : ±1°   | REV                               | A  | UNIT                   | mm                       | PROJECT   |
| X.XX                                 | : ±0.20 | X.XX° | : ±0.5° | DRAW: 黄彬 2023/11/09               |    | CHECKED: 张伟 2023/11/09 | APPROVED: 罗小春 2023/11/09 | PAGE 1/1  |