

	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.09.12	阿树

Technical Data

Material Contact Material: Brass/Phosphor Bronze

Contact plating: Nicker/Gold Flash

Standard: PBT+30%G F




Electrical

Current rating: 3.0Amps/contact ma

Insulator Material: Black Polyester UL94V-0

Withstanding Voltage: 1000V AC/minute Mechanical

Operating temperature: -40 °C to +105 °C



X4602-A 1 NI B

HOUSING COLOR:
B:BLACK BL:BLUE
Y:YELLOW W:WHITE
GR:GREEN R:RED
CONTACT PLATING:
GF:FULL GOLD FLASH
NI:NICKEL
GN:GOLD+NICKEL

— HEIGHT:
1:5.0mm

HOUSING TYPE:
A:OPEN
B:CLOSE
C:LONG

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	

XK13 星城 Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: 2.0 CONN		
CHECKED		UNIT: mm/in	PART NO.: X4602-A1NIB		
APPROVED		SIZE: A4	DWG NO.: X-X4602-A1NIB		
PRECISION CO.,LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A1