



### BEST-102C带开关的温度可调焊接烙铁

- ▶名称: 可调温型电烙铁
- ▶型号: BST-102C
- ▶电压: AC 110V / 220V
- ▶功率: 90W / 60W
- ▶温度范围: 280度-480度
- ▶线长: 130厘米
- ▶包装尺寸: 250 \* 50 \* 42mm
- ▶重量: 200克

Contact Now



### PRODUCT DISPLAY



### PRODUCT SIZE



PRODUCT DETAILS



Temperature indicator: 480°C | 430°C | 380°C | 330°C | 280°C



PRODUCT PHOTOGRAPH



PRODUCT PACKAGING

WEIGHT:191.5G

