



NOTES:
 额定电流 Current rating: 0.5A
 额定电压 Voltage rating: 50V
 耐电压 Withstand voltage: 500V AC/minute
 接触电阻 Contact resistance : $\leq 40m\Omega$
 绝缘电阻 Insulation resistance: 100M Ω MIN
 工作温度 Working temperature: $-25^{\circ}C \sim +85^{\circ}C$

REV.	DESCRIPTION	ECN NO.	NAME	DATE
------	-------------	---------	------	------

Part No	Pin	A	B	C
FPC-11-S4-ICA	4	1.50	7.70	2.56
FPC-11-S5-ICA	5	2.00	8.20	3.06
FPC-11-S6-ICA	6	2.50	8.70	3.56
FPC-11-S7-ICA	7	3.00	9.20	4.06
FPC-11-S8-ICA	8	3.50	9.70	4.56
FPC-11-S9-ICA	9	4.00	10.20	5.06
FPC-11-S10-ICA	10	4.50	10.70	5.56
FPC-11-S11-ICA	11	5.00	11.20	6.06
FPC-11-S12-ICA	12	5.50	11.70	6.56
FPC-11-S13-ICA	13	6.00	12.20	7.06
FPC-11-S14-ICA	14	6.50	12.70	7.56
FPC-11-S15-ICA	15	7.00	13.20	8.06
FPC-11-S16-ICA	16	7.50	13.70	8.56
FPC-11-S17-ICA	17	8.00	14.20	9.06
FPC-11-S18-ICA	18	8.50	14.70	9.56
FPC-11-S19-ICA	19	9.00	15.20	10.06
FPC-11-S20-ICA	20	9.50	15.70	10.56
FPC-11-S21-ICA	21	10.00	16.20	11.06
FPC-11-S22-ICA	22	10.50	16.70	11.56
FPC-11-S23-ICA	23	11.00	17.20	12.06
FPC-11-S24-ICA	24	11.50	17.70	12.56
FPC-11-S25-ICA	25	12.00	18.20	13.06
FPC-11-S26-ICA	26	12.50	18.70	13.56
FPC-11-S27-ICA	27	13.00	19.20	14.06
FPC-11-S28-ICA	28	13.50	19.70	14.56
FPC-11-S29-ICA	29	14.00	20.20	15.06
FPC-11-S30-ICA	30	14.50	20.70	15.56
FPC-11-S31-ICA	31	15.00	21.20	16.06
FPC-11-S32-ICA	32	15.50	21.70	16.56
FPC-11-S33-ICA	33	16.00	22.20	17.06
FPC-11-S34-ICA	34	16.50	22.70	17.56
FPC-11-S35-ICA	35	17.00	23.20	18.06

PCB Layout

适用FFC寸法
Applicable FFC

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM. TOL.		TITLE: FPC 0.5mm间距立式贴片带锁正向Connector(窄扣)			
.x ±0.38		DWG. NO.: FPC-11-SX-ICA			
.xx ±0.20		CHECKED: MAX			
.xxx ±0.05		PART NO.: FPC-11-SX-ICA			
GENERAL ANGLE:		DRAWN: ELLA			
.X ±5°		APPROVED: WILL			
.XX ±3°		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4
.XXX ±1°		LAYER: bxconn			

序号	品名	材料规格	电镀方式/颜色	使用数量	备注
4	FPC 0.5mm间距一焊片	PhosphorBronze T=0.20MM	镀锡	2 PCS	
3	FPC 0.5mm间距一锁扣(窄扣)	LCP/PPS	黑色	1 PCS	
2	FPC 0.5mm间距立贴-PIN	PhosphorBronze T=0.20MM	镀锡/全金	N PCS	
1	FPC 0.5mm间距贴一基座	LCP/PA46/PPS	米色	1 PCS	

